




Pagtutukoy	
Pangalan ng Produkto	8 tono adjustable105dB panlabas Sunog at emerhensiyang paggamit alarma strobe light sirena
Modelo	EB-162
Sukat	126 * 120 * 107 (mm)
Paggawa boltahe	DC 12 ~ 30V
Kasalukuyang alarm	& lt; 40mA (ayon sa paraan ng pagtatrabaho)
Presyon ng tunog	105db
Pinagmulan ng audio	8 tone at liwanag na kumbinasyon (malayang naaayos)
Ligh flash cycle	& lt; 1.3s
Paggawa temperatura	-20 °C ~ 50 °C
Pag-install ng Way	Wall hanging
Tagapagsalita ng alarm	Red LED Light
Operating humidity	95% RH
Imbakan temperatura	-20 °C ~ 60 °C

Kulay	Pula
Timbang	0.4kg

ano ang mga tampok ng aming EB-162 strobe siren?



1.Wired outdoor emergency flash strobe siren

2.DC 12V~30V power supply

3.Operating current $\leq$ 40mA

4.Sound pressure 105db


5.8 sound and flash light models are adjustable freely

6.2 years warranty , welcome OEM


IN-KIND SHOOTING






PAANO GAMITIN ANG ITO



Front




Side



VOLUME



Turn "-" reduce the volume
Turn "+" increase the volume



WATT 100 120 150 200 300

Code setting	Operating Voltage DC12V, switch "NO" to "g"		
Switch 123	Sound species	Pulse description	DB level
LLL/000	119	High level 180uS, low level max:180uS, min:80uS	116(+/-2db)
HHL/110	Last "di" 0.7hz	High level 85uS, low level 890uS	110(+/-2db)
LHL/010	Sounding "da"	High level 115uS, low level 400uS	114(+/-2db)
HLL/100	High sound 119	High level 100uS, low level max:1150uS, min:360uS	115(+/-2db)
LHL/011	Normal 120	High level 180uS, low level max:2090uS, min:1620uS	116(+/-2db)
HLL/101	High sounding "di"	High level 95uS, low level 930uS	111(+/-2db)
LHL/001	120 with fast	High level 180uS, low level max:2090uS, min:1620uS	114(+/-2db)
HHL/111	High sound 120 with fast	High level 140uS, low level max:1100uS, min:950uS	116(+/-2db)

8 Types
Voice & light combination
freely adjustable



Suitable for all kinds of emergency situation!



STANDARD PACKING



TAMPOK NA PRODUKTO

SMQT
铭汗科技



SMQT
铭汗科技



SMQT
铭汗科技



SMQT
铭汗科技



SMQT
铭汗科技



SMQT
铭汗科技



SMQT
铭汗科技



SMQT
铭汗科技




SMQT
铭汗科技



IPAKITA ANG TANGGAPAN



CUSTOMER



PAG-IBIG



SERTIPIKASYON



PAANO MAGAGAMIT



PACKAGING & SHIPPING

Detection+Packing+Sealing+Finishing+International Express



Inquiry



Contract



Testing and packing



Receiving



Reply

Receive payment&Product

Delivery



FAQ

Q: Maaari ba akong magkaroon ng sample order?

A: Oo, handa kaming mag-alok ng sample sample order sa iyo para sa kalidad ng pagsubok. Ang mga halo-halong sample ay katanggap-tanggap.

Q: Ano ang lead time?

A: Ang sample ay nangangailangan ng 1-3 araw ng trabaho, ang oras ng mass production ay nangangailangan ng 10-15 araw ng trabaho.

Q: Ano ang iyong MOQ?

A: Walang limitasyon sa MOQ.

Q: Paano mo ipapadala ang mga kalakal at kung gaano katagal dumating ito?

A: Ang sample ay ipapadala sa iyo sa pamamagitan ng opsyonal na serbisyo sa pagpapadala (courier, air, at dagat), o itinalaga ng mamimili, 7-15 araw.

Q: Paano namin magpapatuloy ang order kung mayroon akong logo upang i-print?

A: Una, maghahanda kami ng likhang sining para sa visual na kumpirmasyon. Kung ang kulay at posisyon ay tama, gagawin muna namin ang sampling mula sa pabrika ng sutla sa pag-print at kumuha ng litrato para sa iyong pangalawang kumpirmasyon bago ang produksyon ng masa.