

Controle de acesso de autorização off-line sem controle de teclado à prova de água



Especificação	
Tensão operacional	DC-9-16V
Corrente de trabalho	200mA
Tamanho	80L x 80W x 20H (mm)
Distância de leitura	4-6cm
Tipo de carta	Cartão IC de 13.56MHZ
Capacidade do cartão	4294967296
Temperatura de trabalho	-10 °C ~ 65 °C
Humidade de trabalho	0-95% de umidade relativa
Distância de comunicação	Menos de 100m
Material da habitação	PC Shell
Modo aberto	Cartão / Cartão + Senha / Senha pública

Quais são as características do nosso controlador de acesso de autorização off-line?



Support ISO14443A agreement with software

Waterproof (grade IP65), tamper device

Free Software write card authorization

Open mode: Card/Card+Password/Public code

Card capacity 4294967296, 13.56MHZ IC card

TIRO IN-KIND



APLICAÇÃO



The screenshot displays the 'Card Center' application window. The left-hand sidebar contains a hierarchical menu. Under 'System Management', there are options for 'Database Configuration' and 'Device Management'. Under 'User Card Management', there are several options including 'User Data Management', 'Card Number Management', 'Set Door Authority For', 'Operation Record Query', and 'Issuing Card Record Query'. Under 'Writing Card Management', there are options for 'User Cards', 'Manage Cards', 'Set Black List', 'Cancel Black List', 'Clear Black List', 'Set Opening Door Time', 'Set Reader Serial Number', 'Set System Time', 'Set Public Passwords', 'Set Readers', and 'Issue Cards In Sequence'. The main area of the window is titled 'User Data Management'. It features a table with three columns: 'User Name', 'Room Number', and 'User Name'. Below the table, there are two input fields labeled 'User Name' and 'Room Number', and a 'Query' button. At the bottom of the main area, there are five buttons: 'Add', 'Reset Data', 'Reset Passwords', 'Deleted', and 'Query'. The bottom status bar of the window displays 'Expiry Date: 2024-08-28 00:00:00'.

SHOW CASES

SMQT[®]
铭汗科技



SMQT[®]
铭汗科技



SMQT[®]
铭汗科技




SMQT[®]
铭汗科技



SMQT[®]
铭汗科技



SMQT[®]
铭汗科技



SMQT[®]
铭汗科技



SMQT[®]
铭汗科技



SMQT[®]
铭汗科技



SHOW DO ESCRITÓRIO



CLIENTES



EXIBIÇÃO

2011 Brazil Fair



2012 shen yang Fair




2013 Jinan Fair



2013 Shenzhen Fair



2017 Shenzhen Fair



2012 shen yang Fair



2013 shen yang Fair



2013 Shenzhen Fair



2015 Shenzhen Fair



CERTIFICAÇÃO



COMO COOPERAR

PACKAGING AND SHIPPING



Express Delivery.....!



Perguntas frequentes

P: Posso ter um pedido de amostra?

R: Sim, estamos dispostos a oferecer um pedido de amostra de teste para teste de qualidade. As amostras misturadas são aceitáveis.

P: Qual é o prazo de entrega?

R: Amostra precisa de 1-3 dias úteis, o tempo de produção em massa precisa de 10 a 15 dias úteis.

Q: Qual é o seu MOQ?

A: Não há limite MOQ. Mais quantidade, mais descontos.

P: Como você envia a mercadoria e quanto tempo demora chegar?

R: A amostra será enviada a você por meio do serviço de transporte opcional (mensageiros, ar e mar), ou nomeado pelo comprador, 7-15 dias.

P: Como procederemos a ordem se eu tiver logo para imprimir?

R: Em primeiro lugar, vamos preparar trabalhos de arte para confirmação visual. Se a cor e a posição estiverem corretas, faremos amostragem em primeiro lugar da fábrica de impressão de seda e tiraremos a foto para sua segunda confirmação antes da produção em massa.

***Como entrar em contato conosco?
Clique no botão entrar nos envie o inquérito abaixo.***